

[See all 36 Products in Family](#)

2.0 OD 48mm Dia. Neutral Density Filter



Stock **#29-008** 3 In Stock

-

1

+

A\$260^{.80}

ADD TO CART

Volume Pricing	
Qty 1-10	A\$260.80 each
Qty 11-25	A\$228.80 each
Need More?	Request Quote

Product Downloads

General

Type:

Neutral Density Filter

Physical & Mechanical Properties

Diameter (mm):

48.00

Optical Properties

Optical Density OD (Average):

2.0

Wratten 2	Substrate: ☐
Uncoated	Coating:
1.0	Transmission (%):
400 - 700	Blocking Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 223:
View	Certificate of Conformance:

Product Details

- Available in Large Sizes
- Easily Cut for Custom Sizing
- Kodak Filter No. 96

Kodak Wratten 2 Neutral Density Filters are used in image forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. These ND filters feature tolerances of $\pm 10\%$ of the nominal diffuse density. Although the filters transmit the infrared spectrum, neutrality is controlled only in the visible spectrum. Kodak Wratten 2 Neutral Density Filters are uncoated and have a blocking wavelength range of 400-700nm. All ND filters are 0.1mm in thickness and can be cut for easy custom sizing.

Note: Storage in humid environments can cause the filters to cloud and temperatures should not exceed 50°C for extended periods. Every 0.3 density increment equals one f-stop.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools