

[See all 33 Products in Family](#)

20 x 20mm, 800µm Pitch, 0.3° Div., Cyl. Microlens Array VIS-NIR



Stock #72-596 **1 In Stock**

A\$1,188⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$1,188.00 each
Qty 11-25	A\$951.00 each
Qty 26-49	A\$891.00 each
Need More?	Request Quote

Product Downloads

General

Lens Array Type:

Physical & Mechanical Properties

20.0 x 20.0 ±0.10 Dimensions (mm):

78.000 Radius R (mm):

Thickness (mm):
2.00 ±0.10

Optical Properties

Effective Focal Length EFL (mm):
173.50 @ 1064nm

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
VIS-NIR (400-1000nm)

Wavelength Range (nm):
400 - 1000

Coating Specification:
R_{abs} ≤0.25% @ 880nm @ 0° AOI
R_{avg} ≤1.25% @ 400 - 870nm @ 0° AOI
R_{avg} ≤1.25% @ 890 - 1000nm @ 0° AOI

Divergence Angle (°):
0.3 (Full Width)

Pitch (µm):
800.00

Array Type:
Single-Sided

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.

Coating Curves