

TECHSPEC[®] 20 x 20mm Protected Silver Coated, λ /10 ZERODUR® Mirror



Stock #39-909 3-5 DAYS

-

1

+

A\$195.20

ADD TO CART

Qty 1-5
A\$195.20
Qty 6+
A\$156.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 λ /10 (measured before coating)

Substrate: 

Back Surface:
Commercial Polish

Surface Quality:

20-10
Dimensions (mm): 20.0 x 20.0 +0.00/-0.20
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 3.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Length (mm): 20.00
Width (mm): 20.00
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.5 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant