

TECHSPEC®

20.0mm Dia. x 80.0mm FL, NIR I Coated, Plano-Convex Lens



Stock **#48-763** 3-5 DAYS

[Other Coating Options](#)



1



A\$66.40

ADD TO CART

Qty 1-9

A\$66.40

Qty 10+

A\$59.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
80.00 @ 587.6nm

Back Focal Length BFL (mm): 78.45
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.35 ±0.10
Edge Thickness ET (mm): 1.13
Radius R₁ (mm): 41.48
Clear Aperture CA (mm): 19
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant