

200µm 0.22 NA UV/VIS Fiber, 10m Length



Stock **#57-068** CLEARANCE **7 In Stock**

A\$128⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$128.00 each
Need More?	Request Quote

Product Downloads

General

Fiber ends are not polished.

Note:

Physical & Mechanical Properties

Cladding Diameter (µm):
220 ±4

Minimum Bend Radius (mm):
44/22 (Continuous/Momentary)

Length (m):
10.00

Outer Diameter (μm):
239 \pm 5

Core Diameter (μm):
200 \pm 4

Optical Properties

Acceptance Angle ($^\circ$):
25.4

Coating:
UV/MS

Substrate:
Fused Silica

Numerical Aperture NA:
0.22

Index of Refraction (n_d) - Core:
1.457

Index of Refraction (n_d) - Cladding:
1.439

Wavelength Range (nm):
190 - 1250

Numerical Aperture (NA) Tolerance:
 \pm 0.02

Material Properties

Buffer Material:
Polyimide

Environmental & Durability Factors

Operating Temperature ($^\circ\text{C}$):
-190 to +390

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

UV/VIS Optical Fibers

- High OH Content
- Fused Silica Core
- Stepped Index
- Multimode Fiber

VIS/NIR Optical Fibers

- Low OH Content
- Ideal for Use with NIR Diode Lasers
- Fused Silica Core
- Stepped Multimode Fiber

Buffered Fiber Optics are ideal for regions of the UV/Visible and Visible/NIR spectrum not covered by our plastic optical fibers. These fibers have a fused silica core and cladding, as well as a polymer buffer for added protection. Fiber diameters of 50 μm – 600 μm feature a high temperature, high strength polyimide buffer, while the 1mm fibers are buffered with nylon for greater protection. Buffered Fiber Optics are offered in UV/MS or VIS/NIR Fibers in 10 and 25m lengths, from 50 to 600 μm .

Note: Fiber ends are not polished.

Technical Information



