

[See all 102 Products in Family](#)

20.4mm Diameter x 25mm FL, MgF₂ Coated, PCX Condenser Lens



Stock #15-533 **5 In Stock**

[Other Coating Options](#)

A\$74⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	A\$74.00 each
Qty 11-49	A\$67.20 each
Need More?	Request Quote

Product Downloads

General

Condenser Lens Type:

Physical & Mechanical Properties

20.40 +0.1/-0.3 Diameter (mm):

≤30 Centering (arcmin):

Center Thickness CT (mm):

5.29 ±0.13

Bevel:

Protective as needed

Shape of Back Surface:

Plano

Optical Properties

Effective Focal Length EFL (mm):

25.00

Numerical Aperture NA:

0.40

Substrate:

Float Glass

Focal Length Tolerance (%):

±7

Coating:

MgF₂ (400-700nm)

Coating Specification:

R_{avg} ≤ 1.75% @ 400 - 700nm

Surface Quality:

80-50 (typical)

f/#:

1.23

Radius R₂ (mm):

Plano

Wavelength Range (nm):

400 - 700

Conjugate Distance:

Infinite

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 235:



Compliant

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information



Coating Curves
