

TECHSPEC® 20mm Dia., 0.66 Numerical Aperture VIS Coated, Aspheric Lens



Stock **#66-319** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$424.00

ADD TO CART

Qty 1-5

A\$424.00

Qty 6+

A\$339.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.1

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 9.16
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤1.5% @ 425 - 675nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 18
Edge Thickness ET (mm): 3.05
Center Thickness CT (mm): 9.60 ±0.1
f/#: 0.75
Bevel: Protective bevel as needed
Radius R₂ (mm): 200
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 425 - 675
Conjugate Distance: Infinite
Power (diopters): 66.67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant