

[See all 16 Products in Family](#)

TECHSPEC® 20mm Dia. 266nm 45°, Nd:YAG Laser Line Mirror



Nd:YAG ZERODUR Laser Line Mirrors

Stock **#26-406** [CONTACT US](#)

⊖ 1 ⊕ **A\$350⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	A\$350.40 each
Qty 6-25	A\$315.20 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

3.00 +/-0.2 **Thickness (mm):**

20.00 +0.00/-0.20 **Diameter (mm):**

Clear Aperture (%):

>90

Parallelism (arcsec):

30

Optical Properties

Substrate:

ZERODUR®

Surface Quality:

20-10

Angle of Incidence (°):

45

Coating:

Laser Mirror (266nm)

Design Wavelength DWL (nm):

266

Reflection at DWL (%):

99.5

Wavelength Range (nm):

263 - 268

Surface Flatness (P-V):

$\lambda/10$

Coating Specification:

$R_{\text{abs}} >99.5\%$ @ 266nm @ 45° AOI $R_{\text{avg}} >99.5\%$ @ 263 - 268nm @ 45° AOI

Coating Type:

Dielectric

Damage Threshold, By Design:

2.5 J/cm² @ 266nm, 20ns, 20Hz

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- ZERODUR® Substrates Provide Near Zero Thermal Expansion
- >99.5% Reflectivity at Nd:YAG Harmonic Frequencies
- High Laser Damage Threshold Specifications

Nd:YAG ZERODUR Laser Line Mirrors combine the extremely low coefficient of thermal expansion of ZERODUR® substrates with the highly reflective TECHSPEC® Nd:YAG mirror coating. Featuring a coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$ these mirrors are ideal for applications where the optics will be exposed to fluctuating temperatures. The Nd:YAG coating offers a high laser damage threshold compatible with both pulsed and continuous wave lasers. Nd:YAG ZERODUR Laser Line Mirrors are designed with precision polished substrates with $\lambda/10$ flatness and 20-10 surface quality. These mirror are an excellent fit for laboratories and integration into larger powerful laser systems