

TECHSPEC[®] 20mm Dia. x 60mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-736-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$176.00

ADD TO CART

Qty 1-5
A\$176.00
Qty 6+
A\$140.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Effective Focal Length EFL (mm):
60.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 56.51
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 19.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 7.00 ±0.20
Center Thickness CT 1 (mm) : 5.00 ±0.10
Center Thickness CT 2 (mm) : 2.00 ±0.10
Radius R₁ (mm) : 35.92
Radius R₂ (mm) : -28.12
Radius R₃ (mm) : -83.79
Edge Thickness ET (mm) : 4.98
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 3.00
Numerical Aperture NA : 0.17
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View