

**TECHSPEC®** 20mm Dia. x 80mm FL, NIR II Coated, Double-Convex Lens



Stock **#67-646** 3-5 DAYS

[Other Coating Options](#)



1



**A\$70.40**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$70.40                      |
| Qty 10+                       |
| A\$63.20                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Diameter (mm):**  
20.00 +0.0/-0.025

**Back Focal Length BFL (mm):**  
78.67

|                                                                                                                                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Effective Focal Length EFL (mm):</b><br>80.00                                                                                                        |
| <b>Coating:</b><br>NIR II (750-1550nm)                                                                                                                  |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                                                                                     |
| <b>Surface Quality:</b><br>40-20                                                                                                                        |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                                   |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                             |
| <b>Centering (arcmin):</b><br><1                                                                                                                        |
| <b>Center Thickness CT (mm):</b><br>4.00                                                                                                                |
| <b>Center Thickness Tolerance (mm):</b><br>±0.10                                                                                                        |
| <b>Edge Thickness ET (mm):</b><br>2.78                                                                                                                  |
| <b>Radius R<sub>1</sub>=R<sub>2</sub> (mm):</b><br>82.00                                                                                                |
| <b>Clear Aperture CA (mm):</b><br>19.00                                                                                                                 |
| <b>f#:</b><br>4.00                                                                                                                                      |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                                                                             |
| <b>Focal Length Tolerance (%):</b><br>±1.00                                                                                                             |
| <b>Numerical Aperture NA:</b><br>0.13                                                                                                                   |
| <b>Type:</b><br>Double-Convex Lens                                                                                                                      |
| <b>Wavelength Range (nm):</b><br>750 - 1550                                                                                                             |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>8 J/cm² @ 1064nm, 10ns                                                                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |