

TECHSPEC® 20mm Dia. x -20mm FL, NIR II, Inked, Double-Concave Lens



Stock **#68-014-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$84.80**

ADD TO CART

Qty 1-9
A\$84.80
Qty 10+
A\$76.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Effective Focal Length EFL (mm):
-20.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: NIR II (750-1550nm)
Type: Double-Concave Lens
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): -20.55
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 19.00
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Edge Thickness ET (mm): 5.03
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Radius R₁=R₂ (mm): -31.82
Surface Quality: 40-20
Damage Threshold, By Design: 8 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View