

TECHSPEC[®] 20mm Dia. x 25mm FL, YAG-BBAR Coated, Inked, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-258-INK** 10-15 DAYS

- 1 +

A\$92.00

ADD TO CART

Qty 1-9

A\$92.00

Qty 10+

A\$82.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Back Focal Length BFL (mm):
23.86

Effective Focal Length EFL (mm): 25.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate:  N-SF11
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.35
Radius R₁=R₂ (mm): 38.34
Clear Aperture CA (mm): 19.00
f/#: 1.25
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.40
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 2500

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View