

TECHSPEC[®] 20mm N-SF11 Uncoated Equilateral Prism



Equilateral Prisms

Stock **#49-431** 20+ In Stock

-

1

+

A\$214⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$214.40 each
Qty 6-25	A\$171.20 each
Qty 26-49	A\$160.80 each
Need More?	Request Quote

Product Downloads

General	
Equilateral Prism	Type:
Physical & Mechanical Properties	
20.00	Length of Face (mm):
20.00	Length (mm):

Dimensional Tolerance (mm):	
±0.1	
Optical Properties	
Uncoated	Coating:
N-SF11	Substrate: ☐
40-20	Surface Quality:
±2	Angle Tolerance (arcmin):
Dispersion	Image Orientation:
400 - 2500	Wavelength Range (nm):
2.50	Power (fringes) @ 632.8nm:
0.50	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for Light Dispersion
- Sizes Ranging from 5 - 50mm
- Available Uncoated or Anti-Reflection Coated
- Additional [Equilateral Prism](#) Options Available

TECHSPEC® Equilateral Prisms feature three equal 60° angles and are often referred to as dispersing prisms. Equilateral prisms are ideal for wavelength separating applications and light dispersion. These prisms are available in sizes ranging from 5-50mm. Our TECHSPEC® Equilateral Prisms are offered uncoated or with a single layer MgF2 anti-reflection coating. Additional [Equilateral Prism](#) options are available.

Technical Information

