

2.0" x 2.0", FL -0.85", Aspheric Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#46-394** 3-5 DAYS



1



A\$53.60

ADD TO CART

Qty 1-10

A\$53.60

Qty 11+

A\$48.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):

-21.59

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 2.0 x2.0
Dimensions (mm): 50.8 x50.8
Effective Diameter (inches): 1.3
Effective Focal Length EFL (inches): -0.85
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): ≤80
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View