

TECHSPEC® 20X, 1064nm Vega® Nd:YAG Laser Line Beam Expander



TECHSPEC® Vega™ Laser Line Beam Expanders



Stock **#35-121** 3-5 DAYS

− 1 +

A\$1,251.20

ADD TO CART

Qty 1-9

A\$1,251.20

Qty 10+

A\$1,105.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm): 1064
Entrance Aperture (mm): 4.5
Exit Aperture (mm): 32
Expansion Power: 20X
Substrate: Fused Silica (Corning 7980)
Length (mm): 121.30
Mounting Threads: Input: Male M30 x 1 Output: Female M42 x 0.5 (not intended for use)
Transmission (%): >98.5 (nominal)
Type: Beam Expander
Weight (g): 436
Housing Diameter (mm): 48
Transmitted Wavefront, P-V: <λ/10 for 1.1mm input beam (nominal, λ = DWL)
Coating Specification: R_{abs} <0.25% @ 1064nm
Wavelength Range (nm): 1000 - 1140
Style: Fixed Magnification
Damage Threshold, By Design: 10 J/cm² @ 1064nm, 10ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View