


TECHSPEC® 20mm Dia. x 80mm FL UV-AR Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#49-970** 3-5 DAYS

1

A\$244.00

ADD TO CART

Qty 1-5

A\$244.00

Qty 6+

A\$195.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
80.00 @ 587.6nm

Back Focal Length BFL (mm): 77.95
Coating: UV-AR (250-425nm)
Coating Specification: R _{abs} ≤1.0% @ 250 - 425nm R _{avg} ≤0.75% @ 250 - 425nm R _{avg} ≤0.5% @ 370 - 420nm
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.61
Radius R₁ (mm): 36.68
Clear Aperture CA (mm): 19
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 250 - 425
Damage Threshold, Reference:  3 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant