

20X Mitutoyo Plan Apo NIR Infinity Corrected Objective

See More by [Mitutoyo](#)



20X Mtutoyo Plan Apo NIR Infinity Corrected Objective, #46-404

Stock **#46-404** 6 In Stock

-

1

+

A\$6,704⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$6,704.00 each
Need More?	Request Quote

Product Downloads

General	
378-824-16	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm	
Microscope Objective	Type:
Infinity Corrected	Style:
	Manufacturer:

Mitutoyo	
	Note:
Example Application: cutting and trimming of semiconductor wafer and circuits	
Physical & Mechanical Properties	
75.00	Length excluding Threads (mm):
34	Maximum Diameter (mm):
300.00	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
532, 1064	Design Wavelength DWL (nm):
0.32mm	Horizontal Field of View, 1/2" Sensor:
0.44mm	Horizontal Field of View, 2/3" Sensor:
10.00	Focal Length FL (mm):
20X	Magnification:
0.40	Numerical Aperture NA:
0.7	Resolving Power (µm):
1.70	Depth of Field (µm):
1.2	Field of View, 24 Diameter Field Eyepiece (mm):
0.9	Field of View, 18 Diameter Field Eyepiece (mm):
20.0	Working Distance (mm):
480 - 1800	Wavelength Range (nm):
95	Parfocal Length (mm):
N/A	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M26 x36 TPI	Mounting Threads:
Environmental & Durability Factors	
-5 to +45	Operating Temperature (°C):
20 - 80%	Operating Humidity:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Ideal for Bright Field Imaging in UV, Visible, and NIR Spectral Regions
- Excellent Performance at Nd:YAG Laser Lines
- Broad Spectral Ranges



Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives combine the benefits of the standard [M Plan Apo and M Plan Apo SL series objectives](#) with enhanced spectral ranges. The NIR objectives are corrected from 480 to 1800nm and feature enhanced transmission of the fundamental and second harmonic of Nd:YAG lasers for laser cutting applications. The NUV and UV series of objectives also have excellent performance at the second, third, and fourth Nd:YAG harmonics of 532nm, 355nm, and 266nm respectively. Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives are ideal for applications that require a significant distance between the objective lens and the object such as

semiconductor inspection, machine vision, and defect detection. The HR series offers an increased numerical aperture, providing smaller spot sizes and higher resolution.

Accessory Tube Lenses

Accessory Tube Lenses and C-Mount Thread Adapters can be used to adapt the Mitutoyo objectives to additional configurations.

Technical Information



Dimensions (mm)								
Stock No.	M Plan NIR	A	B	C	D	E	F	W.D.
#46-402	5X NIR	57.50	-	23.80	23.00	32.20	34.00	37.50
#46-403	10X NIR	64.50	1.00	25.20	24.80	32.20	34.00	30.50
#46-404	20X NIR	75.00	-	-	-	32.20	34.00	20.00
#46-405	50X NIR	78.00	-	-	-	32.20	34.00	17.00
#46-406	100X NIR	83.00	-	25.00	24.60	32.20	34.00	12.00
#56-982	50X NIR HR	85.00	-	-	-	37.00	39.00	10.00
#56-983	100X NIR HR	85.00	-	-	-	37.00	39.00	10.00
#89-350	20X NIR B	69.50	-	-	-	37.00	37.00	25.50
#89-351	50X NIR B	69.50	-	-	-	37.00	37.00	25.50
#37-550*	20X NIR LCD	75.02	-	-	-	32.20	34.00	20.35
Stock No.	M Plan NUV	A	B	C	D	E	F	W.D.
#86-176	10X NUV	64.50	-	25.20	24.80	32.20	34.00	30.50
#46-407	20X NUV	78.00	-	-	-	32.20	34.00	17.00
#46-408	50X NUV	80.00	-	-	-	32.20	34.00	15.00
#46-409	100X NUV	84.00	1.80	25.00	24.00	32.20	34.00	11.00
#86-177	50X NUV HR	85.00	-	-	-	37.00	39.00	10.00
Stock No.	M Plan UV	A	B	C	D	E	F	W.D.
#86-175	10X UV	75.00	-	-	-	32.20	34.00	20.00
#56-320	20X UV	80.00	-	-	-	32.20	34.00	15.00
#56-321	50X UV	83.00	-	-	-	32.20	34.00	12.00
#56-322	80X UV	85.00	-	22.70	-	32.20	34.00	10.00

*LCD 20X parfocal length is 95.37