

[See all 10 Products in Family](#)

2.15" 625nm, Strobed, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock #83-253 [CONTACT US](#)

⊖ 1 ⊕ A\$800⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$800.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

RL2115-66013	Model Number:
50,000	LED Lifetime (hours):
15.00	Number of LEDs:
1.00	Number of Channels:

LED Illuminator **Type of Illumination:**

Optional Manual Intensity Adjustment **Note:** [#86-887](#) and [#89-555](#) are Available

Advanced Illumination **Manufacturer:**

Ring Light **Geometry:**

Strobed **Illumination Mode:**

Physical & Mechanical Properties

55.0 **Height (mm):**

19.0 **Inner Diameter (mm):**

55.0 **Outer Diameter (mm):**

6.4 - 12.7 **Field Coverage (mm):**

Optical Properties

Red **Color:**

625 **Wavelength (nm):**

19 - 25.4 **Working Distance (mm):**

Electrical

30.00 **Maximum Trigger Frequency (Hz):**

30 - 300 **Strobe Duration (µs):**

Hardware & Interface Connectivity

Flying Leads **Connector:**

Power Supply:
Power Supply Required and Sold Separately:
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Threading & Mounting

Standard **Mount:**

M3 x2 **Mounting Threads:**

Environmental & Durability Factors

0 to +65 **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 233:**

Product Details

- Ideal for Visually Enhancing Surface Defects
- Useful for Front or Back Illumination
- 5" Versions Have Variable Intensity

Advanced Illumination Darkfield LED Illuminators are ideal for visually enhancing surface defects. LED intensity can be varied through the in line potentiometer. The 5" darkfield illuminator includes a mounting bracket for easy system integration.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately.

The strobed models' flash duration is dependent on a trigger signal or potentiometer setting. The duration of the strobe can be adjusted from 30 - 300µs via a knob located in the back of the unit. Trigger input signal is CMOS/TTL compatible. The maximum trigger frequency is 30Hz.



Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



[Application Note](#)

Illumination Mounts for Machine Vision Applications
[Read](#)



[Video](#)

Assembly of 3D Printed Mounts for Common Illumination Geometries
[Watch](#)