

2.2 - 13.6um InAsSb Photovoltaic Infrared Detector, PVIA-4TE-13-1x1-TO8-wZnSeAR36



2.2 - 13.6um InAsSb Photovoltaic Infrared Detector, PVA-4TE-13-1x1-TO8-wZnSeAR36

Stock #90-464 NEW **4 In Stock**

⊖ 1 ⊕ **A\$4,040⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	A\$4,040.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

IR Photovoltaic Detector **Type:**

PVA-4TE-13-1x1-TO8-wZnSeAR36 **Model Number:**

TO-8 **Package:**

Vigo Photonics **Manufacturer:**

Physical & Mechanical Properties

7 **Weight (g):**

1.00 x 1.00 **Active Area (mm):**

Optical Properties

2200 - 13600 **Spectral Response (nm):**

36 **Acceptance Angle (°):**

Environmental & Durability Factors

-40 to +70 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Product Details

- Mid and Long-Wave Infrared (MMR/LWIR) Spectral Range
- 1 × 1mm² Active Areas with Acceptance Angles up to 90°
- TO-39 and TO-8 Package Styles with Specialized Anti-Reflection Windows

Vigo Photonics Infrared Detectors deliver high-performance mid and long-wave IR detection with exceptional sensitivity and stability across demanding applications. These HgCdTe and InAsSb detectors are available with a variety of cooling configurations, including single, dual, triple, and quad-stage thermoelectric coolers, to optimize signal-to-noise ratios. Models are offered with active areas of 1 × 1mm² and acceptance angles up to 90°, providing flexibility for system integration. Vigo Photonics Infrared Detectors feature precision packaging options such as TO-39 and TO-8 housings with specialized anti-reflection coatings for maximum throughput. These detectors combine reliability with infrared technology, making them ideal for spectroscopy, gas analysis, and defense applications.