

[See all 12 Products in Family](#)

## 2.45 x 0.70mm, 1.076 ROC, 250µm Pitch, Silicon, 1 x 8 Linear Microlens Array



#21-175, 7.30 x 2.05mm, 0.575 ROC, 750µm Pitch, 1 x 8 Linear Microlens Array

Stock **#21-177** [CONTACT US](#)

⊖ 1 ⊕ **A\$205<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-10   | <b>A\$205.00</b> each         |
| Qty 11-25  | <b>A\$185.00</b> each         |
| Qty 26-49  | <b>A\$175.00</b> each         |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

1 x 8 Linear Array

Type:

Spherical

Lens Profile:

Note:

Linear arrays are centered on the part and surrounded by inactive lenses.

## Physical & Mechanical Properties

0.23 (of each lens) **Diameter (mm):**

0.14 (of each lens) **Clear Aperture CA (mm):**

2.45 x 0.70 ±0.02 **Dimensions (mm):**

1.076 ±3% **Radius R (mm):**

0.50 ±0.025 **Thickness (mm):**

## Optical Properties

Silicon **Substrate:**

BBAR (1250-1620nm) **Coating:**

1250 - 1620 **Wavelength Range (nm):**

$R_{avg} \leq 0.5\%$  @ 1250 - 1620 **Coating Specification:**

1310 **Design Wavelength DWL (nm):**

250 ±0.3 **Pitch (µm):**

0.286 **Working Distance (mm):**

Source: 0.0092  
Target: 0.08 **Mode Field Diameter (mm):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Fused Silica and Silicon Substrates
- 1x4 and 1x8 Lens Array Configurations
- Ideal for Fiber Coupling and Collimating

Linear Microlens Arrays are available in fused silica and silicon substrates with linear arrays of either 4 or 8 lenses. Silicon has a high index of refraction, enabling short focal length, high-NA lens array designs, while fused silica offers excellent thermal stability and visible transmission to facilitate easy alignment. Linear Microlens Arrays are used to collimate and couple fiber arrays in fiber-to-fiber or laser-to-fiber applications, such as with semiconductor laser diodes. These lenses are AR coated for the near-infrared (NIR) with designs for 1310 and 1550nm, making them ideal for use with NIR lasers or in telecommunications.

## Technical Information

LINEAR MICROLENS ARRAYS

| MFD, Source ( $\mu\text{m}$ ) | MFD, Target ( $\mu\text{m}$ ) | Working Distance ( $\mu\text{m}$ ) | Design Wavelength (nm) | Substrate    | Stock No. 1x4 Array | Stock No. 1x8 Array |
|-------------------------------|-------------------------------|------------------------------------|------------------------|--------------|---------------------|---------------------|
| 10.4                          | 85                            | 15 in air, 10 in glue              | 1550                   | Fused Silica | #21-172             | #21-173             |
| 9.2                           | 250                           | 600                                | 1550                   | Fused Silica | #21-174             | #21-175             |
| 9.2                           | 80                            | 286                                | 1310                   | Silicon      | #21-176             | #21-177             |
| 10.4                          | 250                           | 1143                               | 1550                   | Silicon      | #21-178             | #21-179             |
| 9.2                           | 25                            | 1202                               | 1310                   | Silicon      | #21-180             | #21-181             |
| 3.0                           | 250                           | 304                                | 1310                   | Silicon      | #21-182             | #21-183             |

