

[See all 17 Products in Family](#)

2.5" Diameter, Uncoated Plastic Polycarbonate Window



Stock #71-537 **13 In Stock**

- 1 + A\$48⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$48.00 each
Qty 6-25	A\$38.40 each
Qty 26-49	A\$36.80 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Physical & Mechanical Properties

57.15 **Clear Aperture CA (mm):**

2.50 ±0.010 **Diameter (inches):**

Diameter (mm):
63.50 ±2.54

Thickness (inches):
0.060 ±0.003

Thickness (mm):
1.52 ±0.08

Bevel:
Protective as needed

Edges:
Smooth, Machined

Optical Properties

Coating:
Uncoated

Substrate:
Polycarbonate

Index of Refraction (n_d):
1.585

Abbe Number (v_d):
34

Wavelength Range (nm):
425 - 1600

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):
68

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- High Visible Light Transmission
- Excellent Thermal Stability
- Durable and Lightweight
- [Acrylic \(PMMA\) Plastic Windows](#) Also Available

Polycarbonate Plastic Windows are a lightweight alternative to glass windows. Combining durability and high transmission, these windows are an ideal cost-effective solution for harsh environments and displays. Compared to PMMA acrylic windows, polycarbonate windows are more impact resistant and stronger but are more susceptible to scratches. Polycarbonate Plastic Windows feature lower water absorption and a higher softening temperature than PMMA, but their higher index of refraction leads to higher Fresnel reflections without AR coatings. Their strength and stability make these windows ideal for use in medical and industrial applications.

Technical Information

