

2.5 OD, 12.5mm Dia., NIR II Coated, Absorptive ND Filter

See More by [Hoya](#)



Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters

Stock **#13-231** [CONTACT US](#)

-

1

+

A\$84.80

ADD TO CART

Qty 1-10

A\$84.80

Qty 11+

A\$73.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50

Optical Density OD (Average):
2.5 ±0.1 @ 400-700nm (Uncoated Filter)

Nominal Optical Density @ Center of Coating:
1.27 @ 1200nm

Glass/Filter Number: Hoya ND-0.3
Substrate: ☐ ND Filter Glass
Coating: NIR II (750-1550nm)
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 490
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 0.3 (average) @ 400 - 700nm
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Wavelength Range (nm): 750 - 1550
Stock No. of Uncoated Filter: #48-532

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant