

TECHSPEC® 25 x 35mm Protected Gold, λ/4 Mirror



Stock #32-434 3-5 DAYS

- 1 + **A\$144.00**

ADD TO CART

Qty 1-5
A\$144.00
Qty 6+
A\$115.20
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate:
BOROFLOAT®

Back Surface:
Fine Ground

Surface Quality:

60-40
Dimensions (mm): 25.0 x 35.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Length (mm): 35.00
Width (mm): 25.00
Damage Threshold, Reference:  0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant