



[See all 17 Products in Family](#)

TECHSPEC[®]

25.0mm Dia. x -200 FL, 1064nm V-Coat, UV Plano-Concave Lens



Stock **#21-041** 2 In Stock

-

1

+

A\$262⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$262.40 each
Qty 6-25	A\$209.60 each
Qty 26-49	A\$196.80 each
Need More?	Request Quote

Product Downloads

General	
Plano-Concave Lens	Type:
Max. Flat Annulus is 0.3mm	Note:
Physical & Mechanical Properties	

25.00 +0.0/-0.025	Diameter (mm):
2.50	Center Thickness CT (mm):
±0.10	Center Thickness Tolerance (mm):
<1	Centering (arcmin):
24	Clear Aperture CA (mm):
3.32	Edge Thickness ET (mm):

Optical Properties	
-200.00	Effective Focal Length EFL (mm):
Fused Silica (Corning 7980)	Substrate:
8.00	f/#:
0.06	Numerical Aperture NA:
1064nm V-Coat	Coating:
-201.71	Back Focal Length BFL (mm):
R _{abs} <0.25% @ 1064nm	Coating Specification:
1064	Design Wavelength DWL (nm):
587.6	Focal Length Specification Wavelength (nm):
±1	Focal Length Tolerance (%):
-91.69	Radius R ₁ (mm):
40-20	Surface Quality:
15 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Negative Focal Lengths for Beam Expansion or Light Projection Applications
 - Research-Grade Synthetic Fused Silica Substrate
 - <0.25% Reflection at 1064nm for Nd:YAG and Fiber Laser Applications
 - Uncoated and BBAR Coating Options Available
- TECHSPEC® 1064nm Laser Line Coated UV Fused Silica Plano-Concave (PCV) Lenses are high performance lenses that feature a low coefficient of thermal expansion. Manufactured using research-grade synthetic fused silica, these lenses provide excellent transmission and chemical purity. TECHSPEC® 1064nm Laser Line Coated UV Fused Silica Plano-Concave (PCV) Lenses are designed for maximum throughput at 1064nm, making them ideal for applications utilizing Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

