

[See all 7 Products in Family](#)

25.0/25.4mm Optic Dia., E-Series Kinematic Mount



#15-866: 25.0/25.4mm Optic Dia., E-Series Kinematic Mbunt



Stock **#15-866** **3 In Stock**

-

1

+

A\$69^{.60}

ADD TO CART

Volume Pricing	
Qty 1-9	A\$69.60 each
Qty 10-49	A\$66.40 each
Need More?	Request Quote

Product Downloads

General	
Adjustable - Tip-Tilt	Type:
Circular	Type of Optics:
2	Number of Adjustment Screws:

Available in Quick Start Kit: #17-521		Note:
Physical & Mechanical Properties		
23	Clear Aperture CA (mm):	
	Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings	
±3.5	Fine Tilt Angle (°):	
±3.5	Fine Tip Angle (°):	
0.25	Adjustment Screw Pitch (mm):	
2	Min. Thickness of Compatible Optics (mm):	
25.40	Optical Axis Height (mm):	
Threading & Mounting		
25.0 - 25.4	Size of Compatible Optics (mm):	
M6 x 1.0, M4 x 0.7, 8-32	Compatible Post:	
Regulatory Compliance		
Compliant	RoHS 2015:	
View	Certificate of Conformance:	
Compliant	Reach 247:	

Product Details

- Essential Mount for Experiments and OEM System
- Economic Price
- 0.5"- 4.0" Dia. Versions Available
- M6 x 0.25 (101.6 TPI) Adjustment Screws

E-Series Kinematic Optical Mirror Mounts offer many high value features essential for applications in R&D, prototyping, and system integration. The mounts are offered with 2 screws for tip and tilt optical adjustment and alignment (±3.5°). The M6 x 0.25 (101.6 TPI) adjustment screws provide smooth movement and can be driven by hand or by Allen key (2mm key size). The adjustment screw knobs are removable to create a more compact form factor. E-Series Kinematic Optical Mirror Mounts feature mounting holes with both a counterbore designed to accommodate M4 or 8-32 mounting hardware, and M6 x 1.0 internal threads for increased mounting versatility and direct compatibility to [TECHSPEC® Stainless Steel Mounting Posts](#) and [Pedestal Posts](#).

Technical Information

E-SERIES KINEMATIC CIRCULAR OPTICAL MOUNTS					
A (mm)	B (mm)	C (mm), Nominal	Optical Diameter D1 (mm)	Clear Aperture D2 (mm)	Stock No.
25.4	43.5	39.5	12.7/12.5	10	#15-865
25.4	43.5	39.5	25.4/25.0	23	#15-866
38.1	70.1	41.5	50.8/50.0	49	#15-867
50.8	98.9	49.5	76.2/75	72	#15-868
63.5	123.5	54.5	101.6/100	97	#15-869
					