

TECHSPEC® 25.4 x 177.8mm EFL 90° Bare Gold 100Å Off-Axis Parabolic Mirror



Stock **#35-568** **1 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **A\$798⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	A\$798.40 each
Qty 6-10	A\$718.40 each
Qty 11-25	A\$688.00 each
Need More?	Request Quote

Product Downloads

General

Off-Axis Parabolic Mirror **Type:**

Physical & Mechanical Properties

25.40 +0.00/-0.38 **Diameter (mm):**

<100 RMS **Surface Roughness (□):**

90 Clear Aperture (%):

177.8 Y Offset (mm):

Optical Properties

177.80 Effective Focal Length EFL (mm):

±1 Focal Length Tolerance (%):

177.80 Radius of Curvature (mm):

Bare Gold Coating:

Metal Coating Type:

Coating Specification:
R_{avg} ≥ 94% @ 700 - 800nm
R_{avg} ≥ 97% @ 800 - 2,000nm
R_{avg} ≥ 98% @ 2,000 - 12,000nm

90 Off-Set Angle (°):

88.9 Parent Focal Length PFL (mm):

λ/4 Surface Figure, RMS:

700 - 12000 Wavelength Range (nm):

80-50 Surface Quality:

Aluminum 6061-T6 Substrate:

λ/2 Reflected Wavefront, RMS:

Threading & Mounting

#47-111 Compatible Mounting Plates:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:


Compliant Reach 247:

Product Details

- Bare or Protected Gold Coating for NIR and IR Applications
- 50Å and 100Å Surface Roughness Options
- 15°, 30°, 45°, 60°, or 90° Offset Angles
- Aluminum and Silver Coated Mirrors Also Available

TECHSPEC® Gold Off-Axis Parabolic Mirrors (OAPs) are designed for minimal scatter loss in light focusing applications. Available with bare or protected gold coatings, these OAP mirrors offer excellent reflectivity from the near infrared (NIR) to the far infrared (IR). Multiple surface roughness options are available in offset angles from 15 to 90°, providing flexibility for system designs. TECHSPEC® Gold Off-Axis Parabolic Mirrors are commonly used in IR systems such as FLIR and FTIR, as well as IR lasers including quantum cascade lasers (QCLs). Mounting plates with holes perpendicular to the optical axis for post mounting are also available.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
