

[See all 3 Products in Family](#)

# 25.4mm Dia. 20°, 780nm Highly-Dispersive Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) 800nm Highly-Dispersive Ultrafast Mirrors



Stock **#17-067** 5 In Stock

-

1

+

A\$2,080<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | A\$2,080.00 each              |
| Qty 10+        | A\$1,872.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |               |
|----------------------------------|---------------|
| Laser Mirror                     | Type:         |
| HD1608                           | Model Number: |
| Physical & Mechanical Properties |               |

|                   |                       |
|-------------------|-----------------------|
| 10 ±5             | Wedge Angle (arcmin): |
| 80                | Clear Aperture (%):   |
| Commercial Polish | Back Surface:         |
| 25.40 +0.0/-0.5   | Diameter (mm):        |
| 6.35 ±0.20        | Thickness (mm):       |

|                                                                                                                                                 |                                                                                                |
|-------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------|
| Optical Properties                                                                                                                              |                                                                                                |
| >99.8% (typical, p-polarization)                                                                                                                | Reflection at DWL (%):                                                                         |
| R <sub>avg</sub> >99.8%, GDD = -300 fs <sup>2</sup> @ 720 - 840nm (p-polarization)<br>R <sub>abs</sub> >99.8% @ 780nm (typical, p-polarization) | Coating Specification:                                                                         |
| -300fs <sup>2</sup> @ 740 - 840nm                                                                                                               | GDD Specification:                                                                             |
| 720 - 840                                                                                                                                       | Wavelength Range (nm):                                                                         |
| λ/10                                                                                                                                            | Irregularity (P-V) @ 632.8nm:                                                                  |
| Dielectric                                                                                                                                      | Coating Type:                                                                                  |
| Ultrafast (740-840nm)                                                                                                                           | Coating:                                                                                       |
| 780                                                                                                                                             | Design Wavelength DWL (nm):                                                                    |
| 20                                                                                                                                              | Angle of Incidence (°):                                                                        |
| Fused Silica (Corning 7980)                                                                                                                     | Substrate:  |


|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |

## Product Details

- Reflection >99.8% (P-polarization) at 720 – 840nm or 780 – 830nm
- Low Group Delay Dispersion at 5° or 20° AOIs
- Ideal for Pulse Compression of Ti:sapphire Ultrafast Lasers
- [Low GDD Mirrors](#) Also Available

UltraFast Innovations (UFI) 780 and 800nm Highly-Dispersive Ultrafast Mirrors feature an optimized multilayer ultrafast chirped coating based on dispersive optical interference that provides a low group delay dispersion (GDD) and high reflectance. These ultrafast mirrors provide GDDs as low as -1300fs<sup>2</sup> and greater than 99.8% reflectivity for p-polarization. The highly-dispersive design of these ultrafast mirrors offers control of third and higher order dispersions, and provides high beam stability at either 5° or 20° angle of incidence. UltraFast Innovations (UFI) 780 and 800nm Highly-Dispersive Ultrafast Mirrors are ideal for pulse compression and dispersion compensation of ultrafast pulses, such as Ti:sapphire lasers. Standard imperial sizes are available, featuring fused silica substrates.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness

- Tight tolerances and complex geometries
  - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

;