

[See all 2 Products in Family](#)

TECHSPEC® 25.4mm 45°, 2μm Laser Line Mirror



2μm Laser Line Mirrors

Stock **#37-502** **20+ In Stock**

⊖ 1 ⊕ A\$585⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | A\$585.60 each |
| Need More? | Request Quote |

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

Compensating Coating **Back Surface:**

| | |
|---|--|
| 25.40 +0.0/-0.1 | Diameter (mm): |
| 6.35 ±0.2 | Thickness (mm): |
| Optical Properties | |
| 40-20 | Surface Quality: |
| 99.6 | Reflection at DWL (%): |
| 99.6 | Reflectivity (Rs%): |
| 99.9 | Reflectivity (Rp%): |
| Coating Specification: Rs >99.9% @ 1900 – 2200nm Rp >99.6% @ 1940 – 2100nm | |
| 1900 - 2200 | Wavelength Range (nm): |
| λ/7 @ 2000nm | Surface Flatness (P-V): |
| Dielectric | Coating Type: |
| Laser Mirror (1900-2200nm) | Coating: |
| 2000 | Design Wavelength DWL (nm): |
| 45 | Angle of Incidence (°): |
| Fused Silica (Corning 7980) | Substrate: <input type="checkbox"/> |
| >10 J/cm ² @ 2000nm, 10ns, 10Hz | Damage Threshold, By Design: <input type="checkbox"/> |

| | |
|------------------------------|------------------------------------|
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 235: |

Product Details

- Laser Damage Threshold >10 J/cm² @ 2μm, 10ns, 10Hz
 - Designed for Holmium and Thulium Laser Sources
 - λ/7 Surface Accuracy
- TECHSPEC® High Performance 2μm Laser Mirrors are designed for use with Holmium (2100nm) and Thulium (1940nm) doped laser systems. These mirrors are ideal for medical, industrial, and metrology application spaces. The 2 micron wavelength regime is useful for surgical procedures as it can target discrete depth levels of tissue beneath the skin's surface. TECHSPEC® High Performance 2μm Laser Mirrors feature guaranteed laser damage thresholds >10 J/cm² and >99% reflectivity at 2 microns.

Note: For more information on 2μm laser source applications, please see the [Characteristics of 2μm Lasers](#).

Compatible Mounts