

TECHSPEC® 25.4mm Dia., 0.5mm Thick, BBAR (1650-3000nm) AR Coated Sapphire Window



Stock **#21-009** 3-5 DAYS

- 1 + **A\$227.20**

ADD TO CART

Qty 1-24
A\$227.20
Qty 25+
A\$181.60
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o - n_e):

0.008 for Visible Light Orthogonal to Optical Axis

Clear Aperture (%):
≥90

Clear Aperture CA (mm):
22.86

Diameter (mm):
25.40 ±0.05

Thickness (mm):
0.50 ±0.05

Coating:
BBAR (1650-3000nm)

Coating Specification:
R_{avg} <1% @ 1650 - 3000nm
R_{abs} <2% @ 1650 - 3000nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
8.8

Density (g/cm³):
3.97

Edges:
Fine Ground

Index of Refraction n_d:
1.77

Knoop Hardness (kg/mm²):
1900

Parallelism (arcmin):
≤3.5

Poisson's Ratio:
0.27

Substrate:
Sapphire (Al₂O₃)

Surface Flatness (P-V):
2λ (typical)

Surface Quality:
80-50

Type:
Protective Window

Wavelength Range (nm):
1650 - 3000

Young's Modulus (GPa):
435

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)