

## 25.4mm Dia. 1030nm $\lambda/2$ Quartz Waveplate Zero Order



Stock #16-889 3-5 DAYS

- 1 + **A\$780.80**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| A\$780.80 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

Clear Aperture CA (mm):  
20.0

Coating:  
Laser V-Coat (1030nm)

Design Wavelength DWL (nm):  
1030

Diameter (mm):  
25.40 +0.00/-0.25

Substrate: ☐  
Crystal Quartz

|                                                                                           |
|-------------------------------------------------------------------------------------------|
| <b>Retardance:</b><br>λ/2                                                                 |
| <b>Surface Quality:</b><br>20-10                                                          |
| <b>Thickness (mm):</b><br>6.00 +0.00/-0.25                                                |
| <b>Type:</b><br>Crystalline Waveplate                                                     |
| <b>Construction:</b><br>Crystalline                                                       |
| <b>Transmitted Wavefront, P-V:</b><br><λ/10 @ 632.8 nm                                    |
| <b>Parallelism (arcsec):</b><br><3                                                        |
| <b>Retardance Tolerance:</b><br>±λ/300                                                    |
| <b>Temperature Coefficient (λ/°C):</b><br>0.0001                                          |
| <b>Coating Specification:</b><br>R <sub>abs</sub> < 0.2% @ on each surface                |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>>10 J/cm² @ 1064 nm, 10ns |
| <b>Retardance Order:</b><br>0                                                             |
| <b>Configuration:</b><br>Air Spaced                                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |