


25.4mm Dia., 2mm Thick, Uncoated, ISP Optics Cadmium Telluride (CdTe) Window | CD-W-25-2

See More by [ISP Optics](#)



Cadmium Telluride (CdTe) Windows

Stock #16-799 3-5 DAYS

- 1 + **A\$784.00**

ADD TO CART

Qty 1+
A\$784.00
Volume Pricing
Request Quote

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
85

Clear Aperture CA (mm):
21.59

Diameter (mm): 25.40 +0.00/-0.13
Thickness (mm): 2.00 ±0.13
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 5.9
Density (g/cm³): 6.2
Edges: Fine Ground
Index of Refraction n_d: 2.653 @ 10µm
Knoop Hardness (kg/mm²): 54
Parallelism (arcmin): <3
Poisson's Ratio: 0.41
Substrate: Cadmium Telluride (CdTe)
Surface Flatness (P-V): 2λ per inch @632.8nm
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 1000 - 25000
Young's Modulus (GPa): 36.52
Model Number: CD-W-25-2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View