

TECHSPEC® 25.4mm Dia., 650 - 1050nm, 50R:50T, Ultrafast Beamsplitter



TECHSPEC® Ultrafast Beamsplitters

Stock **#13-834** 3-5 DAYS

⊖ 1 ⊕ **A\$408.00**

ADD TO CART

Qty 1-4

A\$408.00

Qty 5+

A\$358.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):
45

Diameter (mm):
25.40 +0.00/-0.10

Substrate: □
[Fused Silica](#) (Corning 7980)

Surface Quality:

10-5
Thickness (mm): 3.00 ±0.10
Type: Ultrafast Non-Polarizing Beamsplitter
Clear Aperture (%): 80
Parallelism (arcsec): <10
Reflection/Transmission Ratio (R/T): 50/50
Coating Specification: Surface 1: R _{avg} = 50±3% @ 650 - 1050nm R _p = 35±3% @ 650 - 1050nm R _s = 67±3% @ 650 - 1050nm Surface 2: R _s <2% @ 650 - 1100nm R _p <1.5% @ 650 - 1100nm
Wavelength Range (nm): 650 - 1050
GDD Specification: Transmission: ±15 fs ² @ 650 - 1100nm Reflectivity: ±15 fs ² @ 650 - 1100nm
Transmitted Wavefront Distortion: λ/8 @ 632.8nm
Reflected Wavefront Distortion: <λ/6 @ 632.8nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View