

25.4mm Dia, 700-1000nm, $\lambda/4$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock #46-560 3-5 DAYS



1



A\$1,392.00

ADD TO CART

Qty 1-5
A\$1,392.00
Qty 6+
A\$1,208.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
11.5

Coating:
R_{avg} <0.6% @ 700 - 1000nm

Diameter (mm):
25.40

Substrate: ☐

Crystal Quartz and MgF ₂
Retardance: λ/4
Surface Quality: 20-10
Thickness (mm): 8.00 ±0.1
Type: Achromatic Waveplate
Parallelism (arcmin): <1
Dimensional Tolerance (mm): +0/-0.25
Construction: Crystalline
Transmitted Wavefront, P-V: λ/4 @ 633nm
Housing Tolerance (mm): +0/-0.25
Retardance Tolerance: ≤ λ/100
Temperature Coefficient (λ/°C): <1/500
Coating Specification: R _{avg} <0.6% @ 700 - 1000nm
Wavelength Range (nm): 700 - 1000
Damage Threshold, By Design: ☐ 500 kV/cm ²
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View