

[See all 1 Products in Family](#)

25.4mm Dia., 1030nm Highly-Dispersive Ultrafast Mirror with Reduced Thermal Lensing

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) 1030nm Highly-Dispersive Ultrafast Mirrors with Reduced Thermal Lensing

Stock **#17-070** **5 In Stock**

-

1

+

A\$1,792^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	A\$1,792.00 each
Qty 10+	A\$1,624.00 each
Need More?	Request Quote

Product Downloads

General	
HD64	Model Number:
Physical & Mechanical Properties	
10	Wedge Angle (arcmin):
80	Clear Aperture (%):

Commercial Polish	Back Surface:
25.40 +0.00/-0.05	Diameter (mm):
6.35 ±0.20	Thickness (mm):
Optical Properties	
R _{avg} >99.5% @ 1010 - 1050nm (5° AOI, p-polarization)	Coating Specification:
-1000fs ² @ 1010 - 1050nm (5° AOI, p-polarization)	GDD Specification:
1010 - 1050	Wavelength Range (nm):
λ/10	Irregularity (P-V) @ 632.8nm:
Dielectric	Coating Type:
Highly Dispersive (1010-1050nm)	Coating:
1030	Design Wavelength DWL (nm):
5	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: □
>0.3 J/cm ² for 1 ps @ 5 kHz rep rate @ 1030nm	Damage Threshold, Reference: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Ultrafast Highly-Dispersive Coating with Reduced Thermal Lensing
 - Highly Negative GDD up to -1000 fs² at 5° AOI
 - >99.5% Minimum Reflection (P-Polarization) across 50nm Bandwidth
 - Ideal for the Generation of High-Power Ultrafast Laser Pulses
- UltraFast Innovations (UFI) 1030nm Highly-Dispersive Ultrafast Mirrors with Reduced Thermal Lensing provide a GDD of -1000fs² and low loss with negligible thermal effects. Thermal lensing can occur if an active gain medium is hotter along the beam axis than the rest of the medium, resulting in a transverse refractive index gradient. This can misalign the laser cavity and lead to different laser mode profiles and drifts in beam pointing. These mirrors are designed to provide a high degree of control over beam stability and feature reflectance >99.5% (P-polarization) between 1010 - 1050nm. At a design angle of incidence (AOI) of 5°, these mirrors maximize the number of reflections between a pair of ultrafast mirrors and allow for pulse compression while limiting thermal lensing. UltraFast Innovations (UFI) 1030nm Highly-Dispersive Ultrafast Mirrors with Reduced Thermal Lensing are ideal for intra-cavity applications, ultrafast high energy oscillators, and amplifiers such as Yb:YAG thin-disk laser systems. Please contact us if your laser system requires a custom size, wavelength, or pulse profile.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).