

25.4mm Dia., $\lambda/2$ at 1030nm and $\lambda/4$ at 515nm, Dual Wavelength Waveplate



Stock #23-751 6 In Stock

-

1

+

A\$689^{.60}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$689.60 each
Qty 6+	A\$627.20 each
Need More?	Request Quote

Product Downloads

General

Type:

Dual Wavelength Waveplate

Physical & Mechanical Properties

Clear Aperture CA (mm):

18.0

Diameter (mm):

25.40 +0/-0.2

Dimensional Tolerance (mm):

+0/-0.2

Parallelism (arcsec):	
<30	
Optical Properties	
Coating:	
R<0.5% @ 515 & 1030nm	
Design Wavelength DWL (nm):	
515, 1030	
Substrate: ☐	
Crystalline Quartz	
Retardance:	
$\lambda/4$ @ 515, $\lambda/2$ @ 1030	
Surface Quality:	
20-10	
Transmitted Wavefront, P-V:	
< $\lambda/10$ @ 632.8nm	
Retardance Tolerance:	
$\lambda/100$ @ 20 °C	
Damage Threshold, By Design: ☐	
>5 J/cm ² @ 1064 nm; 10 ns; 10 Hz	
Retardance Order:	
Multiple order	

Threading & Mounting	
Mount Thickness (mm):	
6 ±0.2	

Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	

Product Details

- $\lambda/4$ and $\lambda/2$ Retardance for Harmonic Separation
- Designed for Nd:YAG, Yb:YAG, or Ti:Sapphire Lasers
- Multiple Order Designs

Dual-Wavelength Quartz Waveplates are made with high-quality crystalline quartz substrates and offer $\lambda/4$ retardance at one wavelength and $\lambda/2$ retardance at a second wavelength. Featuring designed wavelengths for Nd:YAG (532 and 1064nm), Yb:YAG (515 and 1030nm), and Ti:Sapphire (400 and 800nm), these waveplates boast high laser damage threshold (LDT) and anti-reflective (AR) coatings for high powered laser applications. Dual-Wavelength Quartz Waveplates are mounted in a 25.4mm black anodized aluminum ring with an 18mm clear aperture. These waveplates are ideal for laser separation applications requiring increased conversion efficiency of dual-wavelength sources or Second-Harmonic Generation (SHG) lasers through management of polarization.