

TECHSPEC® 25.4mm Dia. x 152.4mm EFL, Protected Aluminum 50Å 90° Off-Axis Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#37-228** CLEARANCE CONTACT US

[Other Coating Options](#)

- 1 + **A\$368.00**

ADD TO CART

Qty 1-5

A\$368.00

Qty 6+

A\$331.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.0/-0.1

Effective Focal Length EFL (mm):
152.40

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 152.40
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥85% @ 400 - 700nm R _{avg} ≥97% @ 2,000 - 12,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 76.2
Surface Figure, RMS: λ/8
Surface Roughness (Angstroms): <50 RMS
Wavelength Range (nm): 400 - 2000
Surface Quality: 80-50
Compatible Mounting Plates: #47-111
Substrate: Aluminum 6061-T6
Y Offset (mm): 152.40
Reflected Wavefront, RMS: λ/4

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View