


25.4mm Dia. 488nm 45°, Low Cost Laser Line Mirror



Stock #39-989 3-5 DAYS

- 1 + **A\$188.80**

ADD TO CART

Qty 1-10
A\$188.80
Qty 11+
A\$168.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Quality:
20-10

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

90
Durability: ML-C-675C
Back Surface: Commercial Polish
Reflection at DWL (%): 99
Coating Specification: R_{abs} >99% @488nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (488nm)
Design Wavelength DWL (nm): 488
Diameter (mm): 25.40 +0.0/-0.1
Thickness (mm): 6.35 ±0.2
Angle of Incidence (°): 45
Substrate: N-BK7

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View