

[See all 4 Products in Family](#)

# 25.4mm Dia., 4mm Thick, 30' Wedge, ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Window | BF-WW-25-4

See More by [ISP Optics](#)



Barium Fluoride (BaF<sub>2</sub>) Wedged Windows



Stock #16-806 **CLEARANCE** 6 In Stock

1 A\$622<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$622.40 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

BF-WW-25-4 **Model Number:**

Protective Window **Type:**

### Physical & Mechanical Properties

21.59	<b>Clear Aperture CA (mm):</b>
25.40 +0.00/-0.13	<b>Diameter (mm):</b>
4.00 ±0.13	<b>Thickness (mm):</b>
Protective as needed	<b>Bevel:</b>
85	<b>Clear Aperture (%):</b>
Fine Ground	<b>Edges:</b>
0.34	<b>Poisson's Ratio:</b>
53	<b>Young's Modulus (GPa):</b>
82.00	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>
30±15 arcmin	<b>Wedge Angle (arcmin):</b>

## Optical Properties

Uncoated	<b>Coating:</b>
<a href="#">Barium Fluoride (BaF<sub>2</sub>)</a>	<b>Substrate:</b> □
1.478 @ 0.5µm 1.451 @ 5µm 1.401 @ 10µm	<b>Index of Refraction (n<sub>d</sub>):</b>
60-40	<b>Surface Quality:</b>
81.78	<b>Abbe Number (v<sub>d</sub>):</b>
200 - 12000	<b>Wavelength Range (nm):</b>
2λ@633nm	<b>Surface Flatness (P-V):</b>

## Material Properties

4.89	<b>Density (g/cm<sup>3</sup>):</b>
18.1	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 240:</b>

## Product Details

- 30 Arcmin Wedge
- Excellent Transmission from 200nm - 12µm
- Resistant to High-Energy Radiation
- [Precision Flat Barium Fluoride \(BaF<sub>2</sub>\) Windows](#) Also Available

ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Windows feature a 30 arcmin wedge to eliminate etalon effects, improving readout in detection and spectroscopy applications. With a low index of refraction of 1.48, these windows provide high transmission from 200nm to 12µm without the need of an anti-reflection (AR) coating. Barium fluoride windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the vacuum ultraviolet range. ISP Optics Barium Fluoride (BaF<sub>2</sub>) Wedged Windows are ideal for infrared spectroscopy, thermal imaging, and general UV-IR detection applications. Barium fluoride is also a fast scintillator and can be used for the detection X-rays, gamma rays, or other high energy particles.

**Note:** These optical windows are very sensitive to thermal shock.

## Technical Information

