

25.4mm Dia. 532.0nm λ /4 Quartz Waveplate Zero Order



Stock #43-696 3-5 DAYS

-

1

+

A\$780.80

ADD TO CART

Qty 1-5

A\$780.80

Qty 6+

A\$632.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
15.00

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm):
532

Diameter (mm):
25.40 +0.00/-0.25

Substrate: Crystal Quartz
Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 7.80 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/10 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View