


25.4mm Dia., 19nm (65eV), 5° EUV/XUV Attosecond Multilayer Flat Mirror

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) EUV/XUV Attosecond Multilayer Mirrors



Stock #16-765

3-5 DAYS



1



A\$3,528.00

ADD TO CART

Qty 1+

A\$3,528.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 ±0.13

Surface Flatness (P-V):
λ/10

Substrate:

[Fused Silica](#) (Coming 7980)

Back Surface: Commercial Polish
Coating Specification: Rs > 38% @ 65eV/19nm
Coating: EUV Multilayer (19nm)
Angle of Incidence (°): 5
Clear Aperture (%): 80
Design Wavelength DWL (nm): 19
Edges: Fine Ground
Parallelism (arcmin): <1
Surface Roughness (Angstroms): <1
Type: Flat Mirror
Center Energy (eV): 65 ±2
Bandwidth (eV): 6
Supported Pulse Duration: 330 attoseconds
Edge Thickness ET (mm): 6.35 ±0.20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant