


[See all 3 Products in Family](#)

25.4mm Dia., 19nm (65eV), 5° EUV/XUV Attosecond Multilayer Flat Mirror

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) EUV/XUV Attosecond Multilayer Mirrors



Stock #16-765 **4 In Stock**

A\$4,032⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$4,032.00 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

330 attoseconds **Supported Pulse Duration:**

XUV65BW6 **Model Number:**

Physical & Mechanical Properties

25.40 ±0.13 **Diameter (mm):**

Commercial Polish **Back Surface:**

80 **Clear Aperture (%):**

Fine Ground **Edges:**

<1 **Parallelism (arcmin):**

<1 **Surface Roughness (□):**

6.35 ±0.20 **Edge Thickness ET (mm):**

Optical Properties

M10 **Surface Flatness (P-V):**

[Fused Silica](#) (Corning 7980) **Substrate:** □

Rs > 38% @ 65eV/19nm **Coating Specification:**

EUV Multilayer (19nm) **Coating:**

5 **Angle of Incidence (°):**

19 **Design Wavelength DWL (nm):**

>38 **Reflection at DWL (%):**

Electrical

65 ±2 **Center Energy (eV):**

6 **Bandwidth (eV):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**



Product Details

- Designed for 330 Attosecond Pulses @65eV (19nm)
- Multilayer Coating with 38% Peak Reflectivity
- ≤1Å (Angstrom) Surface Roughness Superpolished Substrates
- [EUV Flat Mirrors](#) and [EUV Spherical Mirrors](#) Designed at 13.5nm Also Available
- No Minimum Order Quantities, No Coating Lot Charges
- [Platinum-Level 2022 Laser Focus World \(LFW\) Innovators Award](#)

UltraFast Innovations (UFI) Extreme Ultraviolet (EUV/XUV) Attosecond Multilayer Mirrors are designed for steering, focusing, and shaping attosecond pulses. Their multilayer coating is centered at 65eV (19nm) with a 6eV (1.8nm) bandwidth and provides a peak reflectivity of 38% for s-polarized light. These mirrors support EUV pulses with a temporal duration of 330 attoseconds. UFI Extreme Ultraviolet (EUV/XUV) Attosecond Mirrors are ideal for attosecond pulse generation and shaping based on high harmonic generation (HHG), free electron lasers (FELs), or other quantum optical applications.

Atomic precision ion beam deposition results in atomically-smooth coating layers. These mirrors allow for precision control of wavelength and spectral phase with high efficiency in a growing application space. Attosecond science pushes the limits of ultrafast lasers, providing access to some of the most fundamental scientific processes like the motion of electrons. EUV Mirrors are also known as XUV/Soft X-Ray Mirrors. The physical principal behind EUV Attosecond Multilayer Mirrors is the interference of reflected and scattered EUV radiation from each interface of the multilayer stack. Flat and concave mirrors with a 25.4mm diameter are available; please contact us if your application requires an EUV multilayer mirror with a customized center energy, bandwidth, or other specifications.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts