

TECHSPEC®

25.4mm Dia. x 125.0mm FL, NIR II Coated, Plano-Convex Lens



Stock **#38-431** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

A\$66.40

ADD TO CART

Qty 1-9
A\$66.40
Qty 10+
A\$59.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):
125.00 @587.6nm

Back Focal Length BFL (mm): 123.02
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.74
Radius R₁ (mm): 64.60
Clear Aperture CA (mm): 24.4
f#: 4.92
Numerical Aperture NA: 0.10
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: ☐ 8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant