

[See all 2 Products in Family](#)

25.4mm Dia. x -63.5mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF₂) PCV Lens | CF-PC-25-63

See More by [ISP Optics](#)



Stock #24-782 CLEARANCE **1 In Stock**

⊖ 1 ⊕ **A\$270⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-9	A\$270.40 each
Qty 10+	A\$243.20 each
Need More?	Request Quote

Product Downloads

General

Plano-Concave Lens **Type:**

CF-PC-25-63 **Model Number:**

Physical & Mechanical Properties

Diameter (mm):

25.40 +0.00/-0.13

Bevel:

Protective as needed

Center Thickness CT (mm):

2.00 ±0.20

Centering (arcmin):

<3

Clear Aperture CA (mm):

22.86

Edge Thickness ET (mm):

5.40

Optical Properties

Effective Focal Length EFL (mm):

-63.50 @ 5μm

Substrate:

Calcium Fluoride (CaF₂)

f#:

2.50

Numerical Aperture NA:

0.20

Coating:

Uncoated

Wavelength Range (nm):

300 - 8000

Focal Length Tolerance (%):

±2

Radius R₁ (mm):

-25.59

Surface Quality:

60-40

Irregularity (P-V) @ 632.8nm:

λ

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 240:

Compliant

Product Details

- Low Index of Refraction
- IR Grade Calcium Fluoride Substrates
- Standard Imperial Sizes for Easy Benchtop Integration

ISP Optics Calcium Fluoride (CaF₂) Plano-Concave (PCV) Lenses feature IR grade calcium fluoride substrates, providing high transmission in the visible and infrared spectra. Calcium fluoride has a low index of refraction, enabling these lenses to be used without additional Anti-Reflection (AR) coatings. The PCV design diverges incident collimated beams, making them ideal for light projection and beam expansion applications. ISP Optics Calcium Fluoride (CaF₂) Plano-Concave (PCV) Lenses are available in standard imperial sizes with focal lengths ranging from -25.4 to -500mm.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools