


25.4mm Dia. x 250mm EFL, 19nm (65eV), 5° EUV/XUV Attosecond Multilayer Concave Mirror

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) EUV/XUV Attosecond Multilayer Mirrors



Stock #16-766 3-5 DAYS



1



A\$3,528.00

ADD TO CART

Qty 1+
A\$3,528.00

Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 ±0.13

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface: Commercial Polish
Coating Specification: Rs > 38% @ 65eV/19nm
Coating: EUV Multilayer (19nm)
Angle of Incidence (°): 5
Clear Aperture (%): 80
Design Wavelength DWL (nm): 19
Edges: Fine Ground
Surface Roughness (Angstroms): <1
Type: Concave Mirror
Center Energy (eV): 65 ±2
Bandwidth (eV): 6
Supported Pulse Duration: 330 attoseconds
Edge Thickness ET (mm): 6.35 ±0.20
Effective Focal Length EFL (mm): 250.00
Radius of Curvature (mm): 500.00
Radius R₁ (mm): 500.00
Irregularity (P-V) @ 632.8nm: λ/10

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant