

[See all 100 Products in Family](#)

TECHSPEC®

25.4mm Dia. x 25.4mm EFL, Protected Aluminum 50Å Off-Axis Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#87-406** **6 In Stock**

☐ [Other Coating Options](#)

-

1

+

A\$400⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$400.00 each
Qty 6-10	A\$360.00 each
Qty 11-25	A\$344.00 each
Need More?	Request Quote

Product Downloads

General

Type:

Off-Axis Parabolic Mirror

Physical & Mechanical Properties

Diameter (mm):

25.40 +0.0/-0.1

Surface Roughness (□):

<50 RMS	
25.4	Y Offset (mm):
Optical Properties	
25.40	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
25.40	Radius of Curvature (mm):
Protected Aluminum (400-2000nm)	Coating:
Metal	Coating Type:
R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @ 2,000 - 12,000nm	Coating Specification:
90	Off-Set Angle (°):
12.7	Parent Focal Length PFL (mm):
λ/8	Surface Figure, RMS:
400 - 2000	Wavelength Range (nm):
80-50	Surface Quality:
Aluminum 6061-T6	Substrate:
λ/4	Reflected Wavefront, RMS:


Threading & Mounting	
#47-111	Compatible Mounting Plates:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	REACH 201:
View	Certificate of Conformance:

Product Details

- Aluminum Coatings for UV, Visible, and NIR Applications
 - Range of Surface Roughness, Including 50Å and 100Å
 - 15°, 30°, 45°, 60°, or 90° Offset Angle Options
 - Gold and Silver Coated Off-Axis Parabolic Mirrors Also Available
- TECHSPEC® Aluminum Off-Axis Parabolic Mirrors (OAPs) are a cost-effective solution for focusing incident light with minimal scatter loss. Available with enhanced or protected aluminum coatings, these OAP mirrors offer high reflectivity from the ultraviolet (UV) to the near infrared (NIR). These Aluminum OAPs are manufactured with multiple surface roughness specifications, offering designers the choice between high performance, low scatter mirrors and more cost sensitive options. TECHSPEC® Aluminum Off-Axis Parabolic Mirrors are used in optical systems such as Schlieren and spectroscopy systems, as well as in laser systems to focus laser beams. For increased system integration flexibility, mounting plates that thread to the base of these off-axis parabolic mirrors are available.

Technical Information



Typical scatter profiles. Left is standard grade OAPM while right is TECHSPEC® Low Scatter OAPM

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we

provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
