

TECHSPEC® 25.4mm Dia. x 88.9mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#49-782-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$192.00**

ADD TO CART

Qty 1-5
A\$192.00
Qty 6+
A\$153.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 ±0.025

Effective Focal Length EFL (mm):
88.90

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 83.96
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 24.40
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.00 ±0.20
Center Thickness CT 1 (mm) : 6.00 ±0.10
Center Thickness CT 2 (mm) : 4.00 ±0.10
Radius R₁ (mm) : 56.98
Radius R₂ (mm) : -40.06
Radius R₃ (mm) : -162.82
Edge Thickness ET (mm) : 8.07
Substrate : ☐ N-BAK1 / N-SF8
Surface Quality : 40-20
f/# : 3.5
Numerical Aperture NA : 0.14
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View