

TECHSPEC® 25.4mm H x 25.4mm L x 150mm FL VIS 0°, Illumination Grade PCX Cylinder Lens



Stock #36-214 3-5 DAYS

⊖ 1 ⊕ **A\$140.80**

ADD TO CART

Qty 1-5

A\$140.80

Qty 6+

A\$112.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
150.00

Substrate:
[N-BK7](#)

f#:
5.90551181102362

Numerical Aperture NA:

0.08

Coating:

VIS 0° (425-675nm)

Type:

Cylinder Lens, Plano-Convex

Wavelength Range (nm):

425 - 675

Back Focal Length BFL (mm):

148.02

Center Thickness CT (mm):

3.00

Center Thickness Tolerance (mm):

±0.1

Coating Specification: $R_{avg} \leq 0.4\% @ 425 - 675nm$ **Dimensional Tolerance (mm):**

+0.0/-0.2

Dimensions (mm):

25.4 x 25.4

Edge Thickness ET (mm):

1.95

Focal Length Tolerance (%):

±3

Radius R₁ (mm):

77.52

Surface Quality:

60-40

Regulatory Compliance

RoHS 2015:[Compliant](#)**Certificate of Conformance:**[View](#)**Reach 235:**[Compliant](#)