

[See all 11 Products in Family](#)

25.0/25.4mm Optic Dia., 5 Axes Optical Mount



5 Axes Optical Mount



Stock **#13-776** **5 In Stock**

- 1 + A\$1,208⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	A\$1,208.00 each
Qty 5-9	A\$1,148.16 each
Qty 10+	A\$1,027.36 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Linear (XYZ) & Tip-Tilt **Type:**

Circular **Type of Optics:**

Physical & Mechanical Properties

22.0	Clear Aperture CA (mm):
± 2.0 in X and Y, ± 1.5 in Z	Travel (mm):
0.3	Weight (kg):
Black Anodized Aluminum	Construction:
± 2	Tip/Tilt Angle (°):

Threading & Mounting

25.0 - 25.4	Size of Compatible Optics (mm):
12.5 (Max)	Thickness of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

