

TECHSPEC® 25.4mm Square x 50 FL, 355nm AR Coated, Laser Grade PCX Cylinder Lens



Stock **#37-583** 3-5 DAYS

- 1 + **A\$403.20**

ADD TO CART

Qty 1-5
A\$403.20
Qty 6+
A\$323.20
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
50.00

Substrate:
[Fused Silica](#) (Corning 7980)

f/#:
2

Numerical Aperture NA:

0.17
Coating: Laser V-Coat (355nm)
Type: Cylinder Lens, Plano-Convex
Back Focal Length BFL (mm): 46.58
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{abs} <0.25% @ 355nm
Design Wavelength DWL (nm): 355
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.16
Focal Length Specification Wavelength (nm): 587.6
Radius R₁ (mm): 22.93
Surface Quality: 20-10
Damage Threshold, By Design: ☐ 7.5 J/cm² @ 355nm, 20ns, 20Hz
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <3
Power Axis Wedge (arcmin): <4.5
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View