


TECHSPEC®

25.4mm Diameter x 200mm FL, 700-900nm Coated, Ultrafast Thin PCX Lens



Stock #11-660

3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$211.20

ADD TO CART

Qty 1-5

A\$211.20

Qty 6+

A\$185.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
200.23 @ 587.6nm

Back Focal Length BFL (mm):
199.14

Coating: BBAR (700-900nm)
Coating Specification: R_{abs} <0.2% @ 700 - 900nm
Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 0.72
Radius R₁ (mm): 91.80
Clear Aperture CA (mm): 22.86
f/#: 7.88
Numerical Aperture NA: 0.064
Design Wavelength DWL (nm): 800
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 700 - 900
Angle of Incidence (°): 0
Damage Threshold, By Design: 10 J/cm² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View